

**ES EPG 45 AEH 35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Version	35mm <sup>2</sup> , Trapezoidal crimp
Order No.	<a href="#">1501170000</a>
Type	ES EPG 45 AEH 35
GTIN (EAN)	4050118309386
Qty.	1 pc(s).

**ES EPG 45 AEH 35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	180 g
------------	-------

**Crimp inserts**

Crimp cross-section copper	35	Crimping width	19 mm
----------------------------	----	----------------	-------

**Description of contact**

Conductor cross-section, max. AWG	2	Crimping range, max.	35 mm <sup>2</sup>
-----------------------------------	---	----------------------	--------------------

**tool data crimping**

Cable lug cross section	nominal	35 mm <sup>2</sup>
Crimping type/profile	Trapezoidal crimp	

**Classifications**

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ETIM 9.0	EC001282
ECLASS 9.0	21-04-90-90	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-90-90	ECLASS 11.0	21-04-90-90
ECLASS 12.0	21-04-90-90	ECLASS 13.0	21-04-90-90

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	