

ES APG 80 DIN 95**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Version	95mm ² , Indent crimp
Order No.	1502900000
Type	ES APG 80 DIN 95
GTIN (EAN)	4050118310917
Qty.	1 pc(s).

ES APG 80 DIN 95**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	340.3 g
------------	---------

Crimp inserts

Crimp cross-section copper	95	Crimping width	16 mm
Crimping width in mm	16		

Description of contact

Conductor cross-section, max. AWG	3/0	Crimping range, max.	95 mm ²
-----------------------------------	-----	----------------------	--------------------

tool data crimping

Cable lug cross section	nominal	95 mm ²
Crimping type/profile	Indent crimp	

Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ETIM 9.0	EC001282
ECLASS 9.0	21-04-90-90	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-90-90	ECLASS 11.0	21-04-90-90
ECLASS 12.0	21-04-90-90	ECLASS 13.0	21-04-90-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	