

FAD BLK1 SL24**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The front adapters for migration are connected to the old PLC and, by means of a new pre-assembled cable, to the new one. Some adapters have 2 connectors for redundancy.

General ordering data

Order No.	1505520000
Type	FAD BLK1 SL24
GTIN (EAN)	4050118319538
Qty.	1 pc(s).
Delivery status	Discontinued

FAD BLK1 SL24

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	37 mm	Depth (inches)	1.457 inch
Height	24 mm	Height (inches)	0.945 inch
Width	209 mm	Width (inches)	8.228 inch
Net weight	404.33 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Connection data

Connection (field side)	SL 5.08 mm	Connection to PLC	TSX-BLK1
-------------------------	------------	-------------------	----------

Ratings data

Operating voltage	230 V AC / 320 V DC
-------------------	---------------------

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	230 V AC
Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1,2/50µs)	2.1 kV	Insulation test voltage AC	1.2 kV

Classifications

ETIM 6.0	EC002584	ETIM 7.0	EC002584
ETIM 8.0	EC002584	ETIM 9.0	EC002584
ECLASS 9.0	27-33-02-92	ECLASS 9.1	27-24-22-92
ECLASS 10.0	27-33-02-92	ECLASS 11.0	27-33-02-92
ECLASS 12.0	27-33-02-92	ECLASS 13.0	27-33-02-92

Approvals

Approvals



ROHS

Conform

Downloads

Catalogues [Catalogues in PDF-format](#)

FAD BLK1 SL24

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

