

ZQV 2.5N/6 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Version	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 6, Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm
Order No.	1527820000
Type	ZQV 2.5N/6 BL
GTIN (EAN)	4050118448610
Qty.	20 pc(s).

ZQV 2.5N/6 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	24.7 mm	Depth (inches)	0.972 inch
Height	2.8 mm	Height (inches)	0.11 inch
Width	28.3 mm	Width (inches)	1.114 inch
Net weight	3.45 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Wemid	Colour	blue
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
Type of mounting	Direct mounting		

Cross-connector

Number of cross-connected terminals	6
-------------------------------------	---

Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

General

Number of poles	6
-----------------	---

Rating data

Rated current	24 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

ZQV 2.5N/6 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

ROHS

Conform

DownloadsApproval/Certificate/Document of Con-
formity[Confirmation of Standards EN 45545-2_2020-10](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[Zuken E3.S](#)

User Documentation

[2434520000_BED-ANL.ZQV_A_REIHE.pdf](#)[StorageConditionsTerminalBlocks](#)[User Manual ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)