

CLI C 02-3 GE NE CD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, yellow |
| Order No. | 1568241058 |
| Type | CLI C 02-3 GE NE CD |
| GTIN (EAN) | 4032248445288 |
| Qty. | 500 pc(s). |

CLI C 02-3 GE NE CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 3.5 mm | Depth (inches) | 0.138 inch |
| Height | 3 mm | Height (inches) | 0.118 inch |
| Width | 3.4 mm | Width (inches) | 0.134 inch |
| Net weight | 0.06 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | |
|--|--------------------------------------|------|
| Colour | yellow | |
| Halogen | Yes | |
| Insulation cross-section, max. | 3 | |
| Material | PVC, soft, without Cadmium | |
| Material colour according to resistance code | 4 | |
| Number of markers per combination | 1 Reel = Conductor and cable markers | |
| Number of markers per packaging unit | Form of supply | Reel |
| Operating temperature range | -30...80 °C | |
| Operating temperature range, max. | 80 °C | |
| Operating temperature range, min. | -30 °C | |
| Printing | Blank | |
| Recommended industries | Process, Machinery | |
| Type of printing | neutral | |
| UL 94 flammability rating | V-0 | |
| Version | CD | |
| Width | 3.4 mm | |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|----------------------------------|---------------------------|
| Conductor O.D. | 1.3 - 3 mm | Conductor O.D., max. | 3 mm |
| Conductor O.D., min. | 1.3 mm | Conductor cross-section, max. | 1.5 mm ² |
| Conductor cross-section, min. | 0.2 mm ² | Cross-section for connected wire | 0.2 - 1.5 mm ² |
| Halogen | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

CLI C 02-3 GE NE CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Product Change Notification

[PCN CableLine_DE](#)

[PCN CableLine_EN](#)

Catalogues

[Catalogues in PDF-format](#)

CLI C 02-3 GE NE CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Similar to illustration