

WQB A/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

| | |
|------------|---|
| Version | Cross-connector (terminal), when screwed in, Number of poles: 3, Pitch in mm (P): 5.10, Insulat- ed: Yes, black |
| Order No. | 1578960000 |
| Type | WQB A/3 |
| GTIN (EAN) | 4008190108960 |
| Qty. | 50 pc(s). |

WQB A/3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 2.5 mm | Depth (inches) | 0.098 inch |
| Height | 23.5 mm | Height (inches) | 0.925 inch |
| Width | 15.28 mm | Width (inches) | 0.602 inch |
| Net weight | 0.86 g | | |

Temperatures

| | | | |
|---------------------|----------------|----------------------------------|-------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., max. | 70 °C |
|---------------------|----------------|----------------------------------|-------|

Material data

| | | | |
|----------|---------------|--------|-------|
| Material | tinned copper | Colour | black |
|----------|---------------|--------|-------|

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|---|
| Explosion-tested version | No | Installation advice | Feed-through (bushing), Direct mounting |
| Type of fixing | when screwed in | | |

Cross-connector

| | | | |
|-------------------------------------|-----------------|---------------------------|------|
| Number of cross-connected terminals | 3 | Rated current, multi-pole | 24 A |
| Type | Cross-connector | | |

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 5.1 mm |
|-----------------|--------|

General

| | | | |
|---------------------|---|-----------------|---|
| Installation advice | Feed-through (bushing), Direct mounting | Number of poles | 3 |
|---------------------|---|-----------------|---|

Rating data

| | |
|---------------|-------|
| Rated voltage | 800 V |
|---------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

WQB A/3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |