

**WQB A/24****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 24, Pitch in mm (P): 5.10, Insu- lated: Yes, black
Order No.	<a href="#">1579000000</a>
Type	WQB A/24
GTIN (EAN)	4008190134211
Qty.	20 pc(s).

## WQB A/24

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	2.5 mm	Depth (inches)	0.098 inch
Height	23.5 mm	Height (inches)	0.925 inch
Width	123.22 mm	Width (inches)	4.851 inch
Net weight	7.18 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., max.	70 °C
---------------------	----------------	----------------------------------	-------

## Material data

Material	tinned copper	Colour	black
----------	---------------	--------	-------

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
Type of fixing	when screwed in		

## Cross-connector

Number of cross-connected terminals	24	Rated current, multi-pole	24 A
Type	Cross-connector		

## Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

## General

Installation advice	Feed-through (bushing), Direct mounting	Number of poles	24
---------------------	---	-----------------	----

## Rating data

Rated voltage	800 V
---------------	-------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Approvals

ROHS	Conform
------	---------

## WQB A/24

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – 18599_WQB_A-24_DXF.dxf</a> <a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>