

**VQB 1.5/50 SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Numerous national and international approvals and qualifications in accordance with a variety of application standards make the W-series a universal connection solution, especially in harsh conditions. The screw connection has long been an established connection element to meet exacting demands in terms of reliability and functionality. And our W-Series is still setting standards.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 50, Pitch in mm (P): 6.20, Insulated: Yes, 17.5 A, black
Order No.	<a href="#">1635120000</a>
Type	VQB 1.5/50 SW
GTIN (EAN)	4008190262761
Qty.	5 pc(s).

## VQB 1.5/50 SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	12.85 mm	Depth (inches)	0.506 inch
Height	306.1 mm	Height (inches)	12.051 inch
Width	4.2 mm	Width (inches)	0.165 inch
Net weight	17 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Colour	black
--------	-------

## System specifications

Version	for cross-connection link
---------	---------------------------

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

## Dimensions

Pitch in mm (P)	6.2 mm
-----------------	--------

## General

Installation advice	Direct mounting	Number of poles	50
---------------------	-----------------	-----------------	----

## Rating data

Rated current	17.5 A
---------------	--------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Environmental Product Compliance

REACH SVHC	/
------------	---

## Approvals

ROHS	Conform
------	---------

### VQB 1.5/50 SW

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">Beipackzettel_VQB1.5.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	