

KV 11-M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG H (HDC halved cable gland), Cable glands, straight, PG 11, 6 mm, OD min. 7.5 - OD max. 12.5 mm, IP65, Brass, nickel-plated
Order No.	1656390000
Type	KV 11-M
GTIN (EAN)	4008190409401
Qty.	10 pc(s).

KV 11-M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	3 mm	Height (inches)	0.118 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	9 g		

Temperatures

Operating temperature	-20 °C...60 °C
-----------------------	----------------

General information

AF size	18 mm	AF size 1	18 mm
AF size 2	18 mm	Cable glands	PG, PG 11
External thread	PG 11	Halogen	Yes
Length of thread	6 mm	Material	Brass, nickel-plated
Notch multi-layer sealing diameter 1	7.5 mm	Notch multi-layer sealing diameter 2	10 mm
Notch multi-layer sealing diameter 3	12.5 mm	O-Ring	NBR
Operating temperature range, max.	60 °C	Operating temperature range, min.	-20 °C
Outer cable diameter, max.	12.5 mm	Outer cable diameter, min.	7.5 mm
Pitch of thread	1.41 mm	Protection degree	IP65
Protection degree with GWDR	IP65	Seal insert	NBR
Sealing	NBR		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	e8f3dd16-18ca-4fe7-869b-76a120217e3a

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	