

KLBUE 2X2-6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1675350000
Type	KLBUE 2X2-6
GTIN (EAN)	4008190450083
Qty.	10 pc(s).

KLBUE 2X2-6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	24 mm	Depth (inches)	0.945 inch
Height	18 mm	Height (inches)	0.709 inch
Width	15 mm	Width (inches)	0.591 inch
Net weight	9.9 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version	For a shield connection
---------	-------------------------

Additional technical data

Explosion-tested version	Yes	Installation advice	Busbar
Type of fixing	Snap-on		

Conductors for clamping (rated connection)

Cable diameter, max.	6 mm	Cable diameter, min.	2 mm
----------------------	------	----------------------	------

Dimensions

Pitch in mm (P)	15 mm
-----------------	-------

General

Installation advice	Busbar
---------------------	--------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ECLASS 9.0	27-14-11-50	ECLASS 9.1	27-14-11-50
ECLASS 10.0	27-14-11-50	ECLASS 11.0	27-14-11-50
ECLASS 12.0	27-14-11-50	ECLASS 13.0	27-25-01-20

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	