


PAGETAB 15/9**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

PageTab are woven-fabric labels in sheet form. Except for the 8 x 20 version, all labels have a black border.

General ordering data

Version	Device markers, Device markers, 9 x 15 mm, yellow
Order No.	1686160000
Type	PAGETAB 15/9
GTIN (EAN)	4008190492533
Qty.	25 pc(s).

Technical data**Dimensions and weights**

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	9 mm	Height (inches)	0.354 inch
Width	15 mm	Width (inches)	0.591 inch
Net weight	10 g		

Temperatures

Operating temperature range	-29...93 °C
-----------------------------	-------------

General data

Adhesive	Permanent acrylic copolymer	
Colour	yellow	
Material	Acrylic-coated fibre webbing	
Material colour according to resistance code	4	
Number of markers per combination	1 Label sheet = 310 Device markers	
Number of markers per packaging unit	7,750	
Number of markers per packaging unit	Form of supply	Label sheet
	Number of combinations per packaging unit	25
	Number of markers per combination	310
Number per sheet	310	
Operating temperature range	-29...93 °C	
Operating temperature range, max.	93 °C	
Operating temperature range, min.	-29 °C	
Printing	Neutral	
Version	Self-adhesive	
Width	15 mm	

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

