

**LM WO 25/68 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

**General ordering data**

Version	LaserMark, Conductor and cable markers, 8.2 - 14.3 mm, 25 x 68 mm, yellow
Order No.	<a href="#">1695731687</a>
Type	LM WO 25/68 GE
GTIN (EAN)	4008190924713
Qty.	10 pc(s).

## LM WO 25/68 GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	25 mm	Height (inches)	0.984 inch
Width	68 mm	Width (inches)	2.677 inch
Net weight	10.2 g		

## Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

## General data

Adhesive	Acrylate		
Colour	yellow		
Halogen	No		
Material	Polyester film		
Material colour according to resistance code	4		
Number of markers per combination	1 Label sheet = 28 Conductor and cable markers		
Number of markers per packaging unit	Number of combinations per packaging unit	10	
	Number of markers per combination	28	
	Form of supply	Label sheet	
Number of markers per packaging unit	280		
Number per sheet	28		
Operating temperature range	-40... 150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Size of labelling field	25 x 17 mm		
Type of printing	neutral		
UL 94 flammability rating	V-0		
Version	Self-adhesive		
Width	68 mm		

## Conductor and cable markers

Conductor O.D.	8.2 - 14.3 mm	Conductor O.D., max.	14.3 mm
Conductor O.D., min.	8.2 mm	Conductor cross-section, max.	70 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Cross-section for connected wire	16 - 70 mm <sup>2</sup>
Halogen	No	Text field height	17 mm
Text field width	25.4 mm		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## LM WO 25/68 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**LM WO 25/68 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

