

**LM WO 36/93 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

Self-adhesive polyester labels which are suitable for A4 office laser printer.

**General ordering data**

Version	LaserMark, Conductor and cable markers, 9.5 - 22.3 mm, 36 x 93 mm, yellow
Order No.	<a href="#">1695741687</a>
Type	LM WO 36/93 GE
GTIN (EAN)	4008190924737
Qty.	10 pc(s).

## LM WO 36/93 GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	36 mm	Height (inches)	1.417 inch
Width	93 mm	Width (inches)	3.661 inch
Net weight	10.1 g		

## Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

## General data

Adhesive	Acrylate		
Colour	yellow		
Halogen	No		
Material	Polyester film		
Material colour according to resistance code	4		
Number of markers per combination	1 Label sheet = 15 Conductor and cable markers		
Number of markers per packaging unit	Number of markers per combination	15	
	Form of supply	Label sheet	
	Number of combinations per packaging unit	10	
Number of markers per packaging unit	150		
Number per sheet	15		
Operating temperature range	-40...150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Size of labelling field	36 x 25 mm		
Type of printing	neutral		
UL 94 flammability rating	V-0		
Version	Self-adhesive		
Width	93 mm		

## Conductor and cable markers

Conductor O.D.	9.5 - 22.3 mm	Conductor O.D., max.	22.3 mm
Conductor O.D., min.	9.5 mm	Conductor cross-section, max.	120 mm <sup>2</sup>
Conductor cross-section, min.	25 mm <sup>2</sup>	Cross-section for connected wire	25 - 120 mm <sup>2</sup>
Halogen	No	Text field height	25 mm
Text field width	35.5 mm		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

## Approvals

ROHS	Conform
------	---------

### LM WO 36/93 GE

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**LM WO 36/93 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

