

SKMU PG9-K GR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU PA (plastic locknut), Locknut, PG 9, 5 mm, Polyamid 6 (PA6 - GF30)
Order No.	1697450000
Type	SKMU PG9-K GR
GTIN (EAN)	4008190880569
Qty.	100 pc(s).

SKMU PG9-K GR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	5 mm	Height (inches)	0.197 inch
Net weight	1.59 g		

Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

General information

AF size 1	22 mm	Cable glands	PG 9
External thread	PG 9	Halogen	No
Internal thread	PG 9	Length of thread	5 mm
Material	Polyamid 6 (PA6 - GF30)	O.D.	25.41 mm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.41 mm	Silicone	No
Thickness	5 mm	UL 94 flammability rating	HB

Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ETIM 9.0	EC000940
ECLASS 9.0	27-14-44-24	ECLASS 9.1	27-14-44-24
ECLASS 10.0	27-14-44-24	ECLASS 11.0	27-14-44-24
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

SKMU PG9-K GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

