

CBH 27/27 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Fastening of cables or bundles with ties into electrical switchgears and cabinets.

General ordering data

Version	Cable ties, 27 x 27 mm, Plastic, 80 N
Order No.	1697960000
Type	CBH 27/27 BK
GTIN (EAN)	4008190883034
Qty.	100 pc(s).

CBH 27/27 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	2 mm	Depth (inches)	0.079 inch
Height	27 mm	Height (inches)	1.063 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	1.6 g		

Temperatures

Operating temperature range	-40...105 °C
-----------------------------	--------------

Installation materials

For re-opening	No	Halogen	No
Material	Plastic	Max. cable tie width	4.8 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-40 °C
Tensile strength	80 N	Tensile strength (Pound-force)	18 lbf
UL 94 flammability rating	V-2	UV-resistant	Yes
Version	Self-adhesive		

Classifications

ETIM 6.0	EC000449	ETIM 7.0	EC000449
ETIM 8.0	EC000449	ETIM 9.0	EC000449
ECLASS 9.0	23-15-90-07	ECLASS 9.1	27-40-07-90
ECLASS 10.0	27-40-07-90	ECLASS 11.0	23-15-25-09
ECLASS 12.0	23-15-25-09	ECLASS 13.0	23-15-25-09

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CBH 27/27 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Dimensional drawing

