

MARKO-C.100X100X100 B/DR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Device markers, Device markers, 100 x 100 mm, yellow
Order No.	1700550001
Type	MARKO-C.100X100X100 B/DR
GTIN (EAN)	4008190896218
Qty.	10 pc(s).

MARKO-C.100X100X100 B/DR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	100 mm	Height (inches)	3.937 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	5.8 g		

Temperatures

Operating temperature range	-29...80 °C
-----------------------------	-------------

General data

Adhesive	Permanent acrylic copolymer		
Colour	yellow		
Colour of printing	black		
Material	Acrylic-coated fibre webbing		
Material colour according to resistance code	4		
Number of markers per combination	1 Label sheet = 3 Device markers		
Number of markers per packaging unit	Form of supply	Label sheet	
	Number of markers per combination	3	
	Number of combinations per packaging unit	10	
Number of markers per packaging unit	30		
Operating temperature range	-29...80 °C		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-29 °C		
Printed characters	Symbols		
Printing	Lightning flash in triangle		
Version	Self-adhesive		
Width	100 mm		

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

MARKO-C.100X100X100 B/DR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

