

WSM 10 Q**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

WSM small plates

- Completely rust-free and acid-resistant
- Embossed characters are still legible when painted
- Also available with custom printing, embossed on a carrier
- Contents of the WSM Service Box, 40 each of: 0-9, A-Ö, +, -, x, /, :, ., ~, =, ü, Earth, Neutral. 200 steel cable ties (200 mm). 30 stainless steel carriers, 48 mm and 60 mm; 20 steel carriers, 84 mm, and 10 steel carriers, 108 mm and 288 mm

General ordering data

Version	Stainless steel markers, Conductor and cable markers, 5.5 x 9.9 mm, silver
Order No.	1712501669
Type	WSM 10 Q
GTIN (EAN)	4008190947446
Qty.	200 pc(s).

WSM 10 Q

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.012 inch
Height	5.5 mm	Height (inches)	0.217 inch
Width	9.9 mm	Width (inches)	0.39 inch
Net weight	0.12 g		

Temperatures

Operating temperature range	500 °C
-----------------------------	--------

General data

Colour	silver	
Halogen	No	
Material	Stainless steel 1.4404	
Number of markers per combination	1 Component part = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Component part
Operating temperature range	500 °C	
Operating temperature range, max.	500 °C	
Orientation of print	horizontal	
Printed characters	Upper-case letters	
Printing	Q	
Type of printing	Standard	
Width	9.9 mm	

Conductor and cable markers

Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²
Cross-section for connected wire	16 - 500 mm ²	Halogen	No

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

WSM 10 Q

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Stainless steel



Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

General ordering data

Type	SCT 4.6/201 C	Version
Order No.	1699810000	Cable ties, 4.6 x 201 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892258	
Qty.	100 pc(s).	
Type	SCT 4.6/520	Version
Order No.	1699920000	Cable ties, 4.6 x 520 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892364	
Qty.	100 pc(s).	
Type	SCT 4.6/838	Version
Order No.	1699940000	Cable ties, 4.6 x 838 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892388	
Qty.	100 pc(s).	
Type	SCT 4.6/360 C	Version
Order No.	1699910000	Cable ties, 4.6 x 360 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892357	
Qty.	100 pc(s).	
Type	SCT 4.6/679	Version
Order No.	1699930000	Cable ties, 4.6 x 679 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892371	
Qty.	100 pc(s).	
Type	SCT 4.6/266 C	Version
Order No.	1699900000	Cable ties, 4.6 x 266 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892340	
Qty.	100 pc(s).	
Type	SCT 4.6/127 C	Version
Order No.	1699800000	Cable ties, 4.6 x 127 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892241	
Qty.	100 pc(s).	

WSM 10 Q

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Holder



WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

General ordering data

Type	WSMH 48MM	Version
Order No.	1774500000	Stainless steel markers, Conductor and cable markers, 48 x 11 mm,
GTIN (EAN)	4032248149292	silver
Qty.	50 pc(s).	
Type	WSMH 288MM	Version
Order No.	1774490000	Stainless steel markers, Conductor and cable markers, 288 x 11 mm,
GTIN (EAN)	4032248149285	silver
Qty.	50 pc(s).	
Type	WSMH 108MM	Version
Order No.	1774530000	Stainless steel markers, Conductor and cable markers, 108 x 11 mm,
GTIN (EAN)	4032248149322	silver
Qty.	50 pc(s).	
Type	WSMH 84MM	Version
Order No.	1774520000	Stainless steel markers, Conductor and cable markers, 84 x 11 mm,
GTIN (EAN)	4032248149315	silver
Qty.	50 pc(s).	
Type	WSMH 60MM	Version
Order No.	1774510000	Stainless steel markers, Conductor and cable markers, 60 x 11 mm,
GTIN (EAN)	4032248149308	silver
Qty.	50 pc(s).	

WSM 10 Q**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Cable tie tools****General ordering data**

Type	WSM TOOL AUTOMATIK	Version
Order No.	1774470000	Stainless steel markers, Conductor and cable markers, 180 x 275 mm,
GTIN (EAN)	4032248149261	silver
Qty.	1 pc(s).	
Type	WSM TOOL MANUELL	Version
Order No.	1774480000	Stainless steel markers, Conductor and cable markers, 210 x 220 mm,
GTIN (EAN)	4032248149278	silver
Qty.	1 pc(s).	