

VG 21-MS54-ZE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG MS ZE (standard brass cable gland strain relief), Cable glands, straight, PG 21, 7 mm, OD min. 9 - OD max. 19 mm, IP65, Brass, nickel-plated
Order No.	1718850000
Type	VG 21-MS54-ZE
GTIN (EAN)	4008190352073
Qty.	50 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2024-08-31
Alternative product	1569110000

Creation date November 4, 2024 10:00:02 PM CET

Catalogue status 26.10.2024 / We reserve the right to make technical changes.

VG 21-MS54-ZE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	31 mm	Height (inches)	1.22 inch
Length	38 mm	Length (inches)	1.496 inch
Net weight	92.2 g		

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

General information

AF size	34 mm	AF size 1	34 mm
AF size 2	30 mm	Cable glands	PG, PG 21
Clamping range, strain relief, max.	21 mm	Clamping range, strain relief, min.	12 mm
External thread	PG 21	Halogen	No
Length of thread	7 mm	Material	Brass, nickel-plated
Operating temperature range, max.	80 °C	Operating temperature range, min.	-20 °C
Outer cable diameter, max.	19 mm	Outer cable diameter, min.	9 mm
Pitch of thread	1.59 mm	Protection degree	IP54
Protection degree with GWDR	IP65	Seal insert	NBR
Sealing	NBR	Torque for cap nut, max.	6.7 Nm
Torque for cap nut, min.	6.7 Nm	Torque for connecting adapter, max.	10 Nm
Torque for connecting adapter, min.	10 Nm		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01
ECLASS 14.0	27-14-08-01		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

VG 21-MS54-ZE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Polyethylene flat gasket - GWDR PO**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG21-PO	Version
Order No.	1719490000	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 21,
GTIN (EAN)	4008190352752	Polyethylene
Qty.	100 pc(s).	

Brass lock nuts, nickel-plated

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU PG21-MS	Version
Order No.	1719200000	SKMU MS (brass locknut), Locknut, PG 21, 3.5 mm, Brass, nickel-
GTIN (EAN)	4008190352424	plated
Qty.	100 pc(s).	

VG 21-MS54-ZE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Neoprene flat gasket - GWDR NP**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG2 1-NP	Version
Order No.	1719590000	GWDR NP (flat gasket - neoprene), Sealing ring, PG 21, Neoprene
GTIN (EAN)	4008190352851	
Qty.	100 pc(s).	