

SKMU EMV PG7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU MS EMV (brass locknut - EMC), Locknut, PG 7, 4.7 mm, Brass, nickel-plated
Order No.	1718900000
Type	SKMU EMV PG7
GTIN (EAN)	4008190352127
Qty.	20 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2024-08-31

SKMU EMV PG7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	4.7 mm	Height (inches)	0.185 inch
Net weight	2.5 g		

General information

AF size 1	15 mm	Cable glands	PG 7
External thread	PG 7	Halogen	No
Internal thread	PG 7	Length of thread	4.7 mm
Material	Brass, nickel-plated	O.D.	17.33 mm
Pitch of thread	1.27 mm		

Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ETIM 9.0	EC000940
ECLASS 9.0	27-14-44-24	ECLASS 9.1	27-14-44-24
ECLASS 10.0	27-14-44-24	ECLASS 11.0	27-14-44-24
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05
ECLASS 14.0	27-14-08-05		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

SKMU EMV PG7

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

