

**SKMU PG29-K SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU PA (plastic locknut), Locknut, PG 29, 7 mm, Polyamid 6 (PA6 - GF30)
Order No.	<a href="#">1719160000</a>
Type	SKMU PG29-K SW
GTIN (EAN)	4008190352387
Qty.	20 pc(s).

**SKMU PG29-K SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	7 mm	Height (inches)	0.276 inch
Net weight	7.25 g		

**Temperatures**

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

**General information**

AF size 1	46 mm	Cable glands	PG 29
External thread	PG 29	Halogen	No
Internal thread	PG 29	Length of thread	7 mm
Material	Polyamid 6 (PA6 - GF30)	O.D.	53.13 mm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.59 mm	Silicone	No
Thickness	7 mm	UL 94 flammability rating	HB

**Classifications**

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ETIM 9.0	EC000940
ECLASS 9.0	27-14-44-24	ECLASS 9.1	27-14-44-24
ECLASS 10.0	27-14-44-24	ECLASS 11.0	27-14-44-24
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## SKMU PG29-K SW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

