

SKMU PG48-K SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU PA (plastic locknut), Locknut, PG 48, 8 mm, Polyamid 6 (PA6 - GF30)
Order No.	1719190000
Type	SKMU PG48-K SW
GTIN (EAN)	4008190352417
Qty.	25 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2024-08-31
Alternative product	1719090000

SKMU PG48-K SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	8 mm	Height (inches)	0.315 inch
Net weight	3.44 g		

Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

General information

AF size 1	70 mm	Cable glands	PG 48
External thread	PG 48	Halogen	No
Internal thread	PG 48	Length of thread	8 mm
Material	Polyamid 6 (PA6 - GF30)	O.D.	80.85 mm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.59 mm	Silicone	No
Thickness	8 mm	UL 94 flammability rating	HB

Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ETIM 9.0	EC000940
ECLASS 9.0	27-14-44-24	ECLASS 9.1	27-14-44-24
ECLASS 10.0	27-14-44-24	ECLASS 11.0	27-14-44-24
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07
ECLASS 14.0	27-14-08-07		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

SKMU PG48-K SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

