

GWDR PG7-NP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 7, Neoprene
Order No.	1719540000
Type	GWDR PG7-NP
GTIN (EAN)	4008190352806
Qty.	100 pc(s).

GWDR PG7-NP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	1.2 mm	Height (inches)	0.047 inch
Net weight	0.25 g		

Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

General information

Cable glands	PG 7	Diameter of sealing ring	17 mm
External thread	PG 7	Halogen	Yes
Inside diameter D2	11.6 mm	Internal thread	PG 7
Material	Neoprene	Number of wires	1
O.D.	17 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Sealing	Neoprene
Silicone	No	Thickness	1.2 mm

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ETIM 9.0	EC001181
ECLASS 9.0	27-43-03-19	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-43-03-19	ECLASS 11.0	27-43-03-19
ECLASS 12.0	27-43-03-19	ECLASS 13.0	27-43-03-19

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

GWDR PG7-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

