

GWDR PG48-NP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 48, Neoprene
Order No.	1719630000
Type	GWDR PG48-NP
GTIN (EAN)	4008190352899
Qty.	5 pc(s).

GWDR PG48-NP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	1.5 mm	Height (inches)	0.059 inch
Net weight	4 g		

Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

General information

Cable glands	PG 48	Diameter of sealing ring	71 mm
External thread	PG 48	Inside diameter D2	59.3 mm
Internal thread	PG 48	Material	Neoprene
Number of wires	1	O.D.	71 mm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Sealing	Neoprene	Silicone	No
Thickness	1.5 mm		

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ETIM 9.0	EC001181
ECLASS 9.0	27-43-03-19	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-43-03-19	ECLASS 11.0	27-43-03-19
ECLASS 12.0	27-43-03-19	ECLASS 13.0	27-43-03-19
ECLASS 14.0	27-43-03-19		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

GWDR PG48-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

