

**EWS M 25X1,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	EWS (drainage device), Compensating element, M 25, 5 mm, Polyamide
Order No.	<a href="#">1719740000</a>
Type	EWS M 25X1,5
GTIN (EAN)	4008190353001
Qty.	20 pc(s).

**EWS M 25X1,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Length	23 mm	Length (inches)	0.906 inch
Net weight	13.25 g		

**Temperatures**

Operating temperature	-20 °C...40
-----------------------	-------------

**Certificate numbers cable gland**

Certificate no. cable gland (ATEX)	PTB 01 ATEX 1128 X	Identification	Ex e II, II 2 GD
------------------------------------	--------------------	----------------	------------------

**General information**

AF size 1	30 mm	Cable glands	metric
External thread	M 25	Length of thread	5 mm
Material	Polyamide	Operating temperature range, max.	40 °C
Operating temperature range, min.	-20 °C	Pitch of thread	1.5 mm
Protection degree	IP54	Torque for connecting adapter, max.	5 Nm
Torque for connecting adapter, min.	5 Nm	UL 94 flammability rating	V-2

**Classifications**

ETIM 6.0	EC000814	ETIM 7.0	EC000814
ETIM 8.0	EC000814	ETIM 9.0	EC000814
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-18-28-17	ECLASS 13.0	27-18-28-17

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### EWS M 25X1,5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

