

**FM 4.2/TS35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Mounting feet are used to mount components that cannot be snapped directly on a DIN rail.

**General ordering data**

|            |   |
|------------|---|
| Version    | Mounting foot on mounting rail, silver, Steel, bright finish, M 4, Width: 14 mm |
| Order No.  | <a href="#">1724580000</a>  |
| Type       | FM 4.2/TS35   |
| GTIN (EAN) | 4008190377717   |
| Qty.       | 40 pc(s).   |

**FM 4.2/TS35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 7 mm    | Depth (inches)  | 0.276 inch |
| Height     | 50.2 mm | Height (inches) | 1.976 inch |
| Width      | 14 mm   | Width (inches)  | 0.551 inch |
| Net weight | 4.5 g   |                 |            |

**Material data**

|          |                      |                |               |
|----------|----------------------|----------------|---------------|
| Material | Steel, bright finish | Surface finish | nickel-plated |
| Colour   | silver               |                |               |

**System specifications**

|         |                        |      |       |
|---------|------------------------|------|-------|
| Version | For the mounting rails | Rail | TS 35 |
|---------|------------------------|------|-------|

**Additional technical data**

|                          |    |                |         |
|--------------------------|----|----------------|---------|
| Explosion-tested version | No | Type of fixing | Snap-on |
|--------------------------|----|----------------|---------|

**Dimensions**

|                  |        |                 |       |
|------------------|--------|-----------------|-------|
| Internal thread  | M 4    | Pitch in mm (P) | 14 mm |
| Fixing dimension | 4.2 mm |                 |       |

**General**

|      |       |                |               |
|------|-------|----------------|---------------|
| Rail | TS 35 | Surface finish | nickel-plated |
|------|-------|----------------|---------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002625    | ETIM 7.0    | EC002625    |
| ETIM 8.0    | EC002625    | ETIM 9.0    | EC002625    |
| ECLASS 9.0  | 27-18-28-07 | ECLASS 9.1  | 23-15-90-90 |
| ECLASS 10.0 | 27-18-28-07 | ECLASS 11.0 | 27-18-28-07 |
| ECLASS 12.0 | 27-18-28-07 | ECLASS 13.0 | 27-18-28-07 |
| ECLASS 14.0 | 27-18-28-07 |             |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |
| Brochures          |   |

## FM 4.2/TS35

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

