

**CLI M 2-4 GE/SW M MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

**Advantages:**

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

**General ordering data**

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 10 - 317 mm, 4 x 11.3 mm, yellow |
| Order No.  | <a href="#">1733651661</a>   |
| Type       | CLI M 2-4 GE/SW M MP   |
| GTIN (EAN) | 4008190398170  |
| Qty.       | 100 pc(s).   |

## CLI M 2-4 GE/SW M MP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 3 mm    | Depth (inches)  | 0.118 inch |
| Height     | 4 mm    | Height (inches) | 0.157 inch |
| Width      | 11.3 mm | Width (inches)  | 0.445 inch |
| Net weight | 0.12 g  |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## General data

|  |  |                |
|--|--|----------------|
| Colour                                       | yellow   |                |
| Colour of printing                           | black  |                |
| Halogen                                      | Yes  |                |
| Material                                     | PVC, soft, without Cadmium                     |                |
| Material colour according to resistance code | 4  |                |
| Number of markers per combination            | 1 Component part = Conductor and cable markers |                |
| Number of markers per packaging unit         | Form of supply                                 | Component part |
| Operating temperature range                  | -30...80 °C                                    |                |
| Operating temperature range, max.            | 80 °C  |                |
| Operating temperature range, min.            | -30 °C   |                |
| Orientation of print                         | horizontal                                     |                |
| Printed characters                           | Upper-case letters                             |                |
| Printing                                     | M  |                |
| Printing method                              | hot-embossing                                  |                |
| Recommended industries                       | Process, Machinery                             |                |
| Type of printing                             | Standard                                       |                |
| UL 94 flammability rating                    | V-0  |                |
| Version                                      | MultiPack                                      |                |
| Width  | 11.3 mm  |                |

## Conductor and cable markers

|                               |                    |                                  |                          |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 10 - 317 mm        | Conductor O.D., max.             | 317 mm                   |
| Conductor O.D., min.          | 10 mm              | Conductor cross-section, max.    | 500 mm <sup>2</sup>      |
| Conductor cross-section, min. | 16 mm <sup>2</sup> | Cross-section for connected wire | 16 - 500 mm <sup>2</sup> |
| Halogen                       | Yes                |                                  |                          |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |
| ECLASS 14.0 | 27-28-11-02 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

## CLI M 2-4 GE/SW M MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |  |
|-----------------------------|--|
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

### CLI M 2-4 GE/SW M MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



Similar to illustration

**CLI M 2-4 GE/SW M MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Holders**

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

**Advantages:**

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | CLI MH 70 HSTR             | Version   |
| Order No.  | <a href="#">0524400000</a> | CableLine, Accessories, 10 - 317 mm, 70 x 11.3 mm, black  |
| GTIN (EAN) | 4008190075057              |   |
| Qty.       | 100 pc(s).                 |   |
| Type       | CLI MH 110 HSTR            | Version   |
| Order No.  | <a href="#">0189400000</a> | CableLine, Accessories, 10 - 317 mm, 110 x 11.3 mm, black |
| GTIN (EAN) | 4008190144784              |   |
| Qty.       | 100 pc(s).                 |   |