

SZS M25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SZS (serrated washer), Retaining toothed washers, M 25, Stainless steel 1.4404 (316L)
Order No.	1736320000
Type	SZS M25
GTIN (EAN)	4008190963521
Qty.	10 pc(s).

SZS M25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	4.5 mm	Height (inches)	0.177 inch
Net weight	6.88 g		

General information

Cable glands	metric	External thread	M 25
Halogen	halogen-free	Inside diameter D2	25.3 mm
Internal thread	M 25	Material	Stainless steel 1.4404 (316L)
O.D.	37.4 mm	Pitch of thread	1.5 mm
Thickness	1.9 mm		

Classifications

ETIM 6.0	EC002345	ETIM 7.0	EC002345
ETIM 8.0	EC002345	ETIM 9.0	EC002345
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

SZS M25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

