

**SKMU M50 MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|            |  |
|------------|--|
| Version    | SKMU MS (brass locknut), Locknut, M 50, 5 mm, Brass, nickel-plated |
| Order No.  | <a href="#">1737040000</a>   |
| Type       | SKMU M50 MS  |
| GTIN (EAN) | 4008190956516  |
| Qty.       | 25 pc(s).  |

**SKMU M50 MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Height     | 5 mm   | Height (inches) | 0.197 inch |
| Net weight | 6.64 g |                 |            |

**General information**

|                 |                      |                  |          |
|-----------------|----------------------|------------------|----------|
| AF size 1       | 57 mm                | Cable glands     | M 50     |
| External thread | M 50                 | Halogen          | No       |
| Internal thread | M 50                 | Length of thread | 5 mm     |
| Material        | Brass, nickel-plated | O.D.             | 62.37 mm |
| Pitch of thread | 1.5 mm               | Thickness        | 5 mm     |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000940    | ETIM 7.0    | EC000940    |
| ETIM 8.0    | EC000940    | ETIM 9.0    | EC000940    |
| ECLASS 9.0  | 27-14-44-24 | ECLASS 9.1  | 27-14-44-24 |
| ECLASS 10.0 | 27-14-44-24 | ECLASS 11.0 | 27-14-44-24 |
| ECLASS 12.0 | 27-14-08-05 | ECLASS 13.0 | 27-14-08-05 |
| ECLASS 14.0 | 27-14-08-05 |             |             |

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | f350dea6-3de1-42c5-a935-c4eb3e9d5e3c |
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |

### SKMU M50 MS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

