

**SKMU M75 MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU MS (brass locknut), Locknut, M 75, 7 mm, Brass, nickel-plated
Order No.	<a href="#">1737060000</a>
Type	SKMU M75 MS
GTIN (EAN)	4008190956530
Qty.	5 pc(s).

**SKMU M75 MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	7 mm	Height (inches)	0.276 inch
Net weight	68.4 g		

**General information**

AF size 1	80 mm	Cable glands	M 75
External thread	M 75	Halogen	No
Internal thread	M 75	Length of thread	7 mm
Material	Brass, nickel-plated	O.D.	98.18 mm
Pitch of thread	1.5 mm	Thickness	7 mm

**Classifications**

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ETIM 9.0	EC000940
ECLASS 9.0	27-14-44-24	ECLASS 9.1	27-14-44-24
ECLASS 10.0	27-14-44-24	ECLASS 11.0	27-14-44-24
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

### SKMU M75 MS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

