

**LM WO 15/70 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

**General ordering data**

Version	LaserMark, Conductor and cable markers, 8.2 - 14.3 mm, 15 x 70 mm, white
Order No.	<a href="#">1759871044</a>
Type	LM WO 15/70 WS
GTIN (EAN)	403224802695 1
Qty.	10 pc(s).

## LM WO 15/70 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	15 mm	Height (inches)	0.591 inch
Width	70 mm	Width (inches)	2.756 inch
Net weight	10.4 g		

## Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

## General data

Adhesive	Acrylate		
Colour	white		
Halogen	No		
Material	Polyester film		
Material colour according to resistance code	9		
Number of markers per combination	1 Label sheet = 52 Conductor and cable markers		
Number of markers per packaging unit	Number of combinations per packaging unit	10	
	Form of supply		Label sheet
	Number of markers per combination	52	
Number of markers per packaging unit	520		
Number per sheet	52		
Operating temperature range	-40...150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Size of labelling field	15 x 30 mm		
Type of printing	neutral		
UL 94 flammability rating	V-0		
Version	Self-adhesive		
Width	70 mm		

## Conductor and cable markers

Conductor O.D.	8.2 - 14.3 mm	Conductor O.D., max.	14.3 mm
Conductor O.D., min.	8.2 mm	Conductor cross-section, max.	50 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Cross-section for connected wire	16 - 50 mm <sup>2</sup>
Halogen	No	Text field height	30 mm
Text field width	14.98 mm		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02
ECLASS 14.0	27-28-11-02		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## LM WO 15/70 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**LM WO 15/70 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

