

BS 35/WSH 2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Accessories, Set of fixings, Steel
Order No.	1760720000
Type	BS 35/WSH 2
GTIN (EAN)	4008190068714
Qty.	10 pc(s).

BS 35/WSH 2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	37 mm	Depth (inches)	1.457 inch
Height	52 mm	Height (inches)	2.047 inch
Width	13 mm	Width (inches)	0.512 inch
Diameter	3 mm	Net weight	30.8 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	grey
----------	-------	--------	------

System specifications

Version	Mounting foot	Rail	TS 35
---------	---------------	------	-------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Interlock	for screw fixing	Type of fixing	when screwed in

Dimensions

Diameter	3 mm	TS 35 offset	26 mm
----------	------	--------------	-------

General

Installation advice	Direct mounting	Rail	TS 35
---------------------	-----------------	------	-------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	