

VG M12-K68 SKS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K SZS (standard plastic cable gland with anti-kink coils), Cable glands, straight, M 12, 8 mm, OD min. 3 - OD max. 6.5 mm, Polyamide 6
Order No.	1776700000
Type	VG M12-K68 SKS
GTIN (EAN)	4032248156122
Qty.	100 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2024-08-31
Alternative product	1772280000

Creation date August 28, 2024 5:59:08 PM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

VG M12-K68 SKS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	55.5 mm	Height (inches)	2.185 inch
Length	63.5 mm	Length (inches)	2.5 inch
Net weight	4.8 g		

Temperatures

Operating temperature	-20 °C...100 °C
-----------------------	-----------------

Certificate numbers cable gland

Certificate no. cable gland (cULus)	E140310
-------------------------------------	---------

General information

AF size	15 mm	AF size 1	15 mm
Cable glands	metric	External thread	M 12
Halogen	Yes	Length of thread	8 mm
Material	Polyamide 6	Operating temperature range, max.	100 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	6.5 mm
Outer cable diameter, min.	3 mm	Pitch of thread	1.5 mm
Protection degree	IP68 - 5 bar (30 min.)	Seal insert	CR
Silicone	No	Tightening torque	2 Nm
Torque for cap nut, max.	2.5 Nm	Torque for cap nut, min.	1.5 Nm
Torque for connecting adapter, max.	2.5 Nm	Torque for connecting adapter, min.	1.5 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01
ECLASS 14.0	27-14-08-01		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

VG M12-K68 SKS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Plastic lock nuts, grey**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M12 - K GR	Version
Order No.	1772440000	SKMU PA (plastic locknut), Locknut, M 12, 5 mm, Polyamid 6 (PA6 -
GTIN (EAN)	4032248130184	GF30)
Qty.	100 pc(s).	

Neoprene flat gasket - GWDR NP

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M12-NP	Version
Order No.	1913320000	GWDR NP (flat gasket - neoprene), Sealing ring, M 12, Neoprene
GTIN (EAN)	4032248543663	
Qty.	50 pc(s).	

VG M12-K68 SKS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Polyethylene flat gasket - GWDR PO**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M12-PO	Version
Order No.	1777920000	GWDR PO (flat gasket - polyethylene), Sealing ring, M 12, Polyethylene
GTIN (EAN)	4032248158188	
Qty.	50 pc(s).	