

VP M63 K54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPK (blanking plug in plastic), Blanking plug, in closed state, M 63, 15 mm, IP65, Polyamid 6 (PA6 - GF30)
Order No.	1776970000
Type	VP M63 K54
GTIN (EAN)	4032248156412
Qty.	5 pc(s).

VP M63 K54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	5 mm	Height (inches)	0.197 inch
Length	8.5 mm	Length (inches)	0.335 inch
Diameter	63 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	14 mm	Net weight	2.28 g

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

General information

Cable glands	metric	Diameter of sealing ring	63 mm
External thread	M 63	Halogen	No
Head diameter	69.5 mm	Length of thread	15 mm
Material	Polyamid 6 (PA6 - GF30)	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Protection degree	IP54	Protection degree with GWDR	IP65
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-33
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05
ECLASS 14.0	27-14-08-05		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

VP M63 K54

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



VP M63 K54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Plastic lock nuts, grey**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M63 - K GR	Version
Order No.	1772510000	SKMU PA (plastic locknut), Locknut, M 63, 8 mm, Polyamid 6 (PA6 -
GTIN (EAN)	4032248130252	GF30)
Qty.	10 pc(s).	

Neoprene flat gasket - GWDR NP

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M63-NP	Version
Order No.	1736290000	GWDR NP (flat gasket - neoprene), Sealing ring, M 63, Neoprene
GTIN (EAN)	4008190956080	
Qty.	10 pc(s).	

VP M63 K54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Polyethylene flat gasket - GWDR PO**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M63-PO	Version
Order No.	1777990000	GWDR PO (flat gasket - polyethylene), Sealing ring, M 63, Polyethylene
GTIN (EAN)	4032248158256	
Qty.	50 pc(s).	