

VP M25-MS65**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|---|
| Version | VPMS (blanking plug in brass), Blanking plug, in closed state, M 25, 7 mm, Brass, nickel-plated |
| Order No. | 1777750000 |
| Type | VP M25-MS65 |
| GTIN (EAN) | 4032248158027 |
| Qty. | 100 pc(s). |

VP M25-MS65**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|----------------------|-------|----------------------|------------|
| Height | 11 mm | Height (inches) | 0.433 inch |
| Length | 11 mm | Length (inches) | 0.433 inch |
| Diameter | 28 mm | Wall thickness, min. | 0.5 mm |
| Wall thickness, max. | 6 mm | Net weight | 14.26 g |

Temperatures

| | |
|-----------------------|-----------------|
| Operating temperature | -40 °C...100 °C |
|-----------------------|-----------------|

General information

| | | | |
|-----------------------------------|----------------------|-----------------------------------|------------------------|
| Cable glands | metric | Diameter of sealing ring | 25 mm |
| External thread | M 25 | Halogen | No |
| Head diameter | 28 mm | Length of thread | 7 mm |
| Material | Brass, nickel-plated | O-Ring | NBR |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Pitch of thread | 1.5 mm | Protection degree | IP68 - 5 bar (30 min.) |
| Sealing | NBR | Silicone | No |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000451 | ETIM 7.0 | EC000451 |
| ETIM 8.0 | EC000451 | ETIM 9.0 | EC000451 |
| ECLASS 9.0 | 27-14-44-25 | ECLASS 9.1 | 27-14-44-33 |
| ECLASS 10.0 | 27-14-44-25 | ECLASS 11.0 | 27-14-44-25 |
| ECLASS 12.0 | 27-14-08-05 | ECLASS 13.0 | 27-14-08-05 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

VP M25-MS65

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

