

GWDR M25-PO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR PO (flat gasket - polyethylene), Sealing ring, M 25, Polyethylene
Order No.	1777950000
Type	GWDR M25-PO
GTIN (EAN)	4032248158218
Qty.	50 pc(s).

GWDR M25-PO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	2 mm	Height (inches)	0.079 inch
Net weight	0.32 g		

Temperatures

Operating temperature	-30 °C...90 °C
-----------------------	----------------

General information

Cable glands	M 25	Diameter of sealing ring	29 mm
External thread	M 25	Inside diameter D2	25 mm
Internal thread	M 25	Material	Polyethylene
Number of wires	1	O.D.	29 mm
Operating temperature range, max.	90 °C	Operating temperature range, min.	-30 °C
Pitch of thread	1.5 mm	Sealing	PE-HD
Silicone	Yes	Thickness	2 mm

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ETIM 9.0	EC001181
ECLASS 9.0	27-43-03-19	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-43-03-19	ECLASS 11.0	27-43-03-19
ECLASS 12.0	27-43-03-19	ECLASS 13.0	27-43-03-19
ECLASS 14.0	27-43-03-19		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

GWDR M25-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

