

VGM32-MS54 ZE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG MS ZE (standard brass cable gland strain relief), Cable glands, straight, M 32, 8 mm, OD min. 17 - OD max. 27 mm, IP65, Brass, nickel-plated
Order No.	1778490000
Type	VGM32-MS54 ZE
GTIN (EAN)	4032248161508
Qty.	25 pc(s).

VGM32-MS54 ZE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	36 mm	Width (inches)	1.417 inch
Length	42 mm	Length (inches)	1.654 inch
Net weight	140.24 g		

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

General information

AF size	39 mm	AF size 1	42 mm
AF size 2	40 mm	Cable glands	metric, M 32
Clamping range, strain relief, max.	30 mm	Clamping range, strain relief, min.	19 mm
External thread	M 32	Halogen	No
Length of thread	8 mm	Material	Brass, nickel-plated
Operating temperature range, max.	80 °C	Operating temperature range, min.	-20 °C
Outer cable diameter, max.	27 mm	Outer cable diameter, min.	17 mm
Pitch of thread	1.5 mm	Protection degree	IP54
Protection degree with GWDR	IP65	Seal insert	NBR
Sealing	NBR	Torque for cap nut, max.	12 Nm
Torque for cap nut, min.	12 Nm	Torque for connecting adapter, max.	18 Nm
Torque for connecting adapter, min.	18 Nm		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

VGM32-MS54 ZE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass lock nuts, natural finish**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M32 MS SC	Version
Order No.	0930640004	SKMU MS (brass locknut), Locknut, M 32, 4 mm, Brass
GTIN (EAN)	4032248976089	
Qty.	20 pc(s).	

Neoprene flat gasket - GWDR NP

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M32-NP	Version
Order No.	1736260000	GWDR NP (flat gasket - neoprene), Sealing ring, M 32, Neoprene
GTIN (EAN)	4008190956059	
Qty.	50 pc(s).	

VGM32-MS54 ZE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass lock nuts, nickel-plated**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M32 MS	Version
Order No.	1737020000	SKMU MS (brass locknut), Locknut, M 32, 4 mm, Brass, nickel-plated
GTIN (EAN)	4008190956493	
Qty.	100 pc(s).	

Polyethylene flat gasket - GWDR PO

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M32-PO	Version
Order No.	1777960000	GWDR PO (flat gasket - polyethylene), Sealing ring, M 32, Polyethylene
GTIN (EAN)	4032248158225	
Qty.	50 pc(s).	

VGM32-MS54 ZE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Nylon flat gasket - KSWN**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWN M32	Version
Order No.	1076650000	KSWN (flat gasket - nylon), Sealing ring, M 32, Nylon 6
GTIN (EAN)	4032248838691	
Qty.	25 pc(s).	

Vulcanised fibre gasket - KSWF

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWF M32	Version
Order No.	1076690000	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 32, Vulcanized
GTIN (EAN)	4032248838622	fibre
Qty.	25 pc(s).	