

SFC 1/21 MC SDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



The SlimFix Clip combines two advantages: its unique closure mechanism offers the reliability of a closed marker with the ease of installation of an open marker. The clip mechanism allows quick and convenient installation of the marker even after the conductor has been installed. SlimFix Clips are suitable for conductors and cables with an outside diameter of up to 5 mm. The large marking surface - up to 30 mm - enables long character strings. The material is halogen-free and complies with flammability rating V2.

Advantages:

- Halogen-free material
- Flammability rating V2
- Fast installation without tools
- Markers in proven MultiCard format
- Available in the heights of 12 mm, 21 mm and 30 mm

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SlimFix Clip, Conductor and cable markers, 2 - 3.5 mm, 21 x 5.8 mm, To customer specification
Order No.	1779090000
Type	SFC 1/21 MC SDR
GTIN (EAN)	4032248163885
Qty.	40 pc(s).
compatible printer	2715590000 2438520000 2438510000

SFC 1/21 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	7 mm	Depth (inches)	0.276 inch
Height	21 mm	Height (inches)	0.827 inch
Width	5.8 mm	Width (inches)	0.228 inch
Net weight	0.34 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Advice label	Colour based on customer requirements (Please send M-Print PRO file)	
Colour	To customer specification	
Colour of printing	black	
Halogen	No	
Material	Polyamide 66	
Number of markers per combination	1 MultiCard = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40...100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Orientation of print	horizontal	
Printed characters	Based on customer requirements (Please send M-Print PRO file)	
Printing method	MC Laser	
Size of labelling field	21 x 4.1 mm	
Type of printing	To customer specification	
UL 94 flammability rating	V-2	
Width	5.8 mm	

Conductor and cable markers

Conductor O.D.	2 - 3.5 mm	Conductor O.D., max.	3.5 mm
Conductor O.D., min.	2 mm	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 2.5 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--