

ZBW 1/3.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Our special tools support within the cabinet process in the area of wiring or also the assembly of the components.

General ordering data

Version	Z-series, Operating tool
Order No.	1781930000
Type	ZBW 1/3.5
GTIN (EAN)	4032248199532
Qty.	1 pc(s).

ZBW 1/3.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	23.75 mm	Depth (inches)	0.935 inch
Height	140.7 mm	Height (inches)	5.539 inch
Width	27.76 mm	Width (inches)	1.093 inch
Net weight	16.522 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-40
Continuous operating temp., max.	100		

Material data

Material	POM	Colour	orange
UL 94 flammability rating	HB		

System specifications

Version	Operating tool
---------	----------------

Additional technical data

Explosion-tested version	No
--------------------------	----

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-04-50-03
ECLASS 12.0	21-04-50-03	ECLASS 13.0	21-04-50-03

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format