

HDC 10B TOBU 1M20G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**IP65**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|--|
| Version | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 20 |
| Order No. | 1787600000 |
| Type | HDC 10B TOBU 1M20G |
| GTIN (EAN) | 4032248204946 |
| Qty. | 1 pc(s). |

HDC 10B TOBU 1M20G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 73 mm | Depth (inches) | 2.874 inch |
| Height | 52 mm | Height (inches) | 2.047 inch |
| Width | 58.5 mm | Width (inches) | 2.303 inch |
| Net weight | 142 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Dimensions

| | | | |
|----------------------|-----------|---------------------|-------|
| Cable entry | w. thread | Height of housing B | 52 mm |
| Total length housing | 73 mm | Width housing C | 43 mm |

General data

| | | | |
|-----------------------------|-----------------------------|-----------------------|-----------------------------|
| EMC housings | No | Housing main material | diecast aluminium |
| Material of locking element | Stainless steel, rust-proof | Protection degree | IP65 (in plugged condition) |
| Surface finish | Powder coating | | |

Version

| | | | |
|------------------------------|----------------------------------|--------------------------------|------------------------------------|
| BG | 4 | Cable entry | w. thread |
| Clamp version | Side-locking clamp | Colour (RAL) | RAL 7035 |
| Design | Standard | Design of housing | Cable entry from top, Plug housing |
| Design of locking system | Side-locking clamp on lower side | Internal thread | M 20 |
| Number of cable entry on top | 1 | Number of cable entry sideways | 0 |
| Size | 4 | Size of cable entries | M 20 |
| Suitable for ModuPlug® | No | Top part/bottom part/lid | upper part |
| Type | Plug | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000437 | ETIM 7.0 | EC000437 |
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ECLASS 9.0 | 27-44-02-02 | ECLASS 9.1 | 27-44-02-02 |
| ECLASS 10.0 | 27-44-02-02 | ECLASS 11.0 | 27-44-02-02 |
| ECLASS 12.0 | 27-44-02-02 | ECLASS 13.0 | 27-44-02-02 |

| | |
|---------------------|-------------------------|
| Substance | Acetone |
| Chemical resistance | Conditionally resistant |
| Substance | Drilling oil |
| Chemical resistance | Resistant |
| Substance | Diesel |
| Chemical resistance | Resistant |
| Substance | Ethyl alcohol |
| Chemical resistance | Resistant |
| Substance | Transmission oil |

HDC 10B TOBU 1M20G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data**

| | |
|---------------------|-------------------------|
| Chemical resistance | Resistant |
| Substance | Hydraulic oil |
| Chemical resistance | Resistant |
| Substance | Coolant |
| Chemical resistance | Resistant |
| Substance | Petroleum benzine |
| Chemical resistance | Resistant |
| Substance | Sweat |
| Chemical resistance | Resistant |
| Substance | Premium gasoline |
| Chemical resistance | Conditionally resistant |
| Substance | Water |
| Chemical resistance | Resistant |
| Substance | UV |
| Chemical resistance | Unstable |
| Substance | Ozone |
| Chemical resistance | Unstable |

Environmental Product Compliance

| | |
|---------------------|---|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | d447edfa-0214-4f34-b5ba-82eae491b46a |
| Chemical resistance | de.myview.objectmodel.impl.BlockImpl@3a2cc22e de.myview.objectmodel.impl.BlockImpl@4b8c5c62 de.myview.objectmodel.impl.BlockImpl@6a22a76 de.myview.objectmodel.impl.BlockImpl@55353359 de.myview.objectmodel.impl.BlockImpl@954a663 de.myview.objectmodel.impl.BlockImpl@20129467 de.myview.objectmodel.impl.BlockImpl@37f4eb89 de.myview.objectmodel.impl.BlockImpl@4b27a9d5 de.myview.objectmodel.impl.BlockImpl@676c696c de.myview.objectmodel.impl.BlockImpl@53e9684a de.myview.objectmodel.impl.BlockImpl@4351791d de.myview.objectmodel.impl.BlockImpl@35ce09a3 de.myview.objectmodel.impl.BlockImpl@316d217f |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

HDC 10B TOBU 1M20G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity

[Manufacturer's declaration](#)

Engineering Data

[CAD data – STEP](#)

Product Change Notification

[20220214 Technical change to HDC housings](#)

[20220214 Technische Änderung bei HDC-Gehäusen](#)

Technical Documentation

[1787600000 HDC_10B_TOBU_1M20G_STP_Blatt_1.pdf](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)


[FL FIELDWIRING EN](#)

HDC 10B TOBU 1M20G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HDC 10B TOBU 1M20G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Cover**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 10B DMDQ 2QB | Version |
| Order No. | 1665240000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cover for upper part of housing, Side-locking clamp on lower side, Standard |
| GTIN (EAN) | 4008190421946 | |
| Qty. | 1 pc(s). | |