

CC-H 15/27**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

General ordering data

Version	ClipCard, Accessories, 15 x 27 mm, black
Order No.	1790410000
Type	CC-H 15/27
GTIN (EAN)	4032248215201
Qty.	45 pc(s).

CC-H 15/27**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	5.5 mm	Depth (inches)	0.217 inch
Height	15 mm	Height (inches)	0.591 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	0.996 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Colour	black	
Halogen	No	
Material	Polyamide 66	
Number of markers per combination	1 MultiCard = Accessories	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40... 100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Recommended industries	Machinery	
UL 94 flammability rating	V-2	
Width	27 mm	

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format