

RF RS 70 LI/A2/O.SG DB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The RS 70 profile is supplied in fixed lengths. The desired length is obtained by connecting the individual pieces together. The PCB is pushed into the side of the profile. End cover plates close off the sides of the profile.. Elements for terminal rails and direct mounting are available here. The clip-on feet are permanently attached to the profile. Marking options are integrated into the side pieces.

General ordering data

Version	Mounting rail housing beige, End plate DIN mounting rail left, Width: 10 mm
Order No.	1795690000
Type	RF RS 70 LI/A2/O.SG DB
GTIN (EAN)	4032248247066
Qty.	20 pc(s).

RF RS 70 LI/A2/O.SG DB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	28.6 mm	Depth (inches)	1.126 inch
Height	70 mm	Height (inches)	2.756 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	5.2 g		

Material data

Comparative Tracking Index (CTI)	600 ≤ CTI	Insulating material	PA 66
UL 94 flammability rating	V-2		

General data

Colour	beige	Colour chart (similar)	RAL 1001
Encapsulation option	No	Protection degree	IP00
Rail	TS 35		

Classifications

ETIM 7.0	EC002779	ETIM 8.0	EC002779
ETIM 9.0	EC002779	ECLASS 11.0	27-18-27-92
ECLASS 12.0	27-18-27-92	ECLASS 13.0	27-19-06-02

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

RF RS 70 LI/A2/O.SG DB
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Drawings

LOCKING-FOOT LEFT

