

**TM 201/15 V0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

**General ordering data**

|            |   |
|------------|---|
| Version    | TM, Socket x 5 mm, PVC, Colour: Transparent, Conductor O.D.: 1.5 - 2.5 mm |
| Order No.  | <a href="#">1798620000</a>  |
| Type       | TM 201/15 V0  |
| GTIN (EAN) | 4032248243358   |
| Qty.       | 1,000 pc(s).  |

## TM 201/15 V0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 5 mm    | Depth (inches)  | 0.197 inch |
| Height     | 15 mm   | Height (inches) | 0.591 inch |
| Width      | 5 mm    | Width (inches)  | 0.197 inch |
| Net weight | 0.265 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -40...80 °C |
|-----------------------------|-------------|

## General data

|                                   |             |                                   |                           |
|-----------------------------------|-------------|-----------------------------------|---------------------------|
| Colour                            | Transparent | Material                          | PVC                       |
| Operating temperature range       | -40...80 °C | Operating temperature range, max. | 80 °C                     |
| Operating temperature range, min. | -40 °C      | Recommended industries            | Transportation, Machinery |
| Type of printing                  | neutral     | UL 94 flammability rating         | V-0                       |
| Width                             | 5 mm        |                                   |                           |

## Conductor and cable markers

|                               |                      |                                  |                            |
|-------------------------------|----------------------|----------------------------------|----------------------------|
| Conductor O.D.                | 1.5 - 2.5 mm         | Conductor O.D., max.             | 2.5 mm                     |
| Conductor O.D., min.          | 1.5 mm               | Conductor cross-section, max.    | 1.5 mm <sup>2</sup>        |
| Conductor cross-section, min. | 0.25 mm <sup>2</sup> | Cross-section for connected wire | 0.25 - 1.5 mm <sup>2</sup> |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">CAD data – STEP</a>  |
| Engineering Data            | <a href="#">Zuken E3.S</a>   |
| Product Change Notification | <a href="#">PCN Transparent Sleeves_DE</a><br><a href="#">PCN Transparent Sleeves_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>   |

## TM 201/15 V0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | TM-I 15 MC NE VI           | Version                                 |
| Order No.  | <a href="#">1427870000</a> | TM-I, Insert markers, 15 x 4 mm, violet |
| GTIN (EAN) | 4050118231847              |   |
| Qty.       | 400 pc(s).                 |   |
| Type       | TM-I 15 MC NE RT           | Version                                 |
| Order No.  | <a href="#">1609981686</a> | TM-I, Insert markers, 15 x 4 mm, red    |
| GTIN (EAN) | 4008190367824              |   |
| Qty.       | 400 pc(s).                 |   |
| Type       | TM-I 15 MC NE WS           | Version                                 |
| Order No.  | <a href="#">1609981044</a> | TM-I, Insert markers, 15 x 4 mm, white  |
| GTIN (EAN) | 4008190914783              |   |
| Qty.       | 400 pc(s).                 |   |
| Type       | TM-I 15 MC NE GE           | Version                                 |
| Order No.  | <a href="#">1609981687</a> | TM-I, Insert markers, 15 x 4 mm, yellow |
| GTIN (EAN) | 4008190914776              |   |
| Qty.       | 400 pc(s).                 |   |
| Type       | TM-I 15 MC NE SI           | Version                                 |
| Order No.  | <a href="#">1609981697</a> | TM-I, Insert markers, 15 x 4 mm, silver |
| GTIN (EAN) | 4008190137410              |   |
| Qty.       | 400 pc(s).                 |   |
| Type       | TM-I 15 MC NE BL           | Version                                 |
| Order No.  | <a href="#">1609981693</a> | TM-I, Insert markers, 15 x 4 mm, blue   |
| GTIN (EAN) | 4008190367831              |   |
| Qty.       | 400 pc(s).                 |   |

**TM 201/15 V0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

|            |                            |  |
|------------|----------------------------|--|
| Type       | TM-I 15 MC NE GN           | Version                                |
| Order No.  | <a href="#">1609981688</a> | TM-I, Insert markers, 15 x 4 mm, green |
| GTIN (EAN) | 4008190398705              |  |
| Qty.       | 400 pc(s).                 |  |