

**TM 206/15 V0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

**General ordering data**

Version	TM, Socket x 27 mm, PVC, Colour: Transparent, Conductor O.D.: 14 - 22 mm
Order No.	<a href="#">1806260000</a>
Type	TM 206/15 V0
GTIN (EAN)	4032248275779
Qty.	200 pc(s).

**TM 206/15 V0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	27 mm	Depth (inches)	1.063 inch
Height	15 mm	Height (inches)	0.591 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	1.56 g		

**Temperatures**

Operating temperature range	-40...80 °C
-----------------------------	-------------

**General data**

Colour	Transparent	Material	PVC
Operating temperature range	-40...80 °C	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Recommended industries	Transportation, Machinery
Type of printing	neutral	UL 94 flammability rating	V-0
Width	27 mm		

**Conductor and cable markers**

Conductor O.D.	14 - 22 mm	Conductor O.D., max.	22 mm
Conductor O.D., min.	14 mm	Conductor cross-section, max.	120 mm <sup>2</sup>
Conductor cross-section, min.	35 mm <sup>2</sup>	Cross-section for connected wire	35 - 120 mm <sup>2</sup>

**Classifications**

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
Product Change Notification	<a href="#">PCN Transparent Sleeves_DE</a> <a href="#">PCN Transparent Sleeves_EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## TM 206/15 V0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	TM-I 15 MC NE VI	Version
Order No.	<a href="#">1427870000</a>	TM-I, Insert markers, 15 x 4 mm, violet
GTIN (EAN)	4050118231847	
Qty.	400 pc(s).	
Type	TM-I 15 MC NE SI	Version
Order No.	<a href="#">1609981697</a>	TM-I, Insert markers, 15 x 4 mm, silver
GTIN (EAN)	4008190137410	
Qty.	400 pc(s).	
Type	TM-I 15 MC NE BL	Version
Order No.	<a href="#">1609981693</a>	TM-I, Insert markers, 15 x 4 mm, blue
GTIN (EAN)	4008190367831	
Qty.	400 pc(s).	
Type	TM-I 15 MC NE GN	Version
Order No.	<a href="#">1609981688</a>	TM-I, Insert markers, 15 x 4 mm, green
GTIN (EAN)	4008190398705	
Qty.	400 pc(s).	
Type	TM-I 15 MC NE RT	Version
Order No.	<a href="#">1609981686</a>	TM-I, Insert markers, 15 x 4 mm, red
GTIN (EAN)	4008190367824	
Qty.	400 pc(s).	
Type	TM-I 15 MC NE WS	Version
Order No.	<a href="#">1609981044</a>	TM-I, Insert markers, 15 x 4 mm, white
GTIN (EAN)	4008190914783	
Qty.	400 pc(s).	

## TM 206/15 V0

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	TM-I 15 MC NE GE	Version
Order No.	<a href="#">1609981687</a>	TM-I, Insert markers, 15 x 4 mm, yellow
GTIN (EAN)	4008190914776	
Qty.	400 pc(s).	