

**WQL 2 WF5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Bolt-type screw terminals, Cross-connector, Number of poles: 2
Order No.	<a href="#">1812710000</a>
Type	WQL 2 WF5
GTIN (EAN)	4032248404568
Qty.	5 pc(s).

## WQL 2 WF5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	4 mm	Depth (inches)	0.157 inch
Height	25 mm	Height (inches)	0.984 inch
Width	12 mm	Width (inches)	0.472 inch
Net weight	8.61 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	Copper - zinc	Colour	grey
----------	---------------	--------	------

## Additional technical data

Explosion-tested version	No	Type of fixing	when screwed in
--------------------------	----	----------------	-----------------

## Cross-connector

Number of cross-connected terminals	2	Rated current, 2-pole	76 A
Rated current, multi-pole	101 A	Type	Cross-connector

## Dimensions

Pitch in mm (P)	15.6 mm
-----------------	---------

## General

Number of poles	2
-----------------	---

## Rating data

Rated current	76 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	