

KLBUE 3-8 SDSC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The shield clamping saddles for direct mounting can be easily and conveniently attached directly to the mounting plate. The products differ in the range of the cable diameter and the thread for fastening the shield clamping saddles.

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1835840000
Type	KLBUE 3-8 SDSC
GTIN (EAN)	4032248394555
Qty.	10 pc(s).

KLBUE 3-8 SDSC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	25.9 mm	Depth (inches)	1.02 inch
Height	18 mm	Height (inches)	0.709 inch
Width	14.4 mm	Width (inches)	0.567 inch
Mounting dimension - width	13.2 mm	Net weight	12.3 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version	For a shield connection
---------	-------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of mounting	Screw		

Conductors for clamping (rated connection)

Cable diameter, max.	8	Cable diameter, min.	3
----------------------	---	----------------------	---

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ECLASS 9.0	27-14-11-50	ECLASS 9.1	27-14-11-50
ECLASS 10.0	27-14-11-50	ECLASS 11.0	27-14-11-50
ECLASS 12.0	27-14-11-50	ECLASS 13.0	27-25-01-20

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	