

**ESG 10/17 MC SDR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|                    |  |
|--------------------|--|
| Version            | ESG, Device markers x 17 mm, PA 66, Colour: To customer specification, pluggable |
| Order No.          | <a href="#">1856710000</a>   |
| Type               | ESG 10/17 MC SDR   |
| GTIN (EAN)         | 4032248400829  |
| Qty.               | 40 pc(s).  |
| compatible printer | <a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a> |

**ESG 10/17 MC SDR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 0.8 mm | Depth (inches)  | 0.031 inch |
| Height     | 10 mm  | Height (inches) | 0.394 inch |
| Width      | 17 mm  | Width (inches)  | 0.669 inch |
| Net weight | 0.37 g |                 |            |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

**General data**

|                                      |   |           |
|--------------------------------------|---|-----------|
| Application/manufacturer             | Allen-Bradley, Festo MT                                       |           |
| Colour                               | To customer specification                                     |           |
| Colour of printing                   | black   |           |
| Halogen                              | No  |           |
| Material                             | PA 66   |           |
| Number of markers per combination    | 1 MultiCard = Device markers                                  |           |
| Number of markers per packaging unit | Form of supply  | MultiCard |
| Operating temperature range          | -40... 100 °C   |           |
| Operating temperature range, max.    | 100 °C  |           |
| Operating temperature range, min.    | -40 °C  |           |
| Printed characters                   | Based on customer requirements (Please send M-Print PRO file) |           |
| Printing method                      | MC Laser  |           |
| UL 94 flammability rating            | V-2   |           |
| Version                              | pluggable   |           |
| Width                                | 17 mm   |           |

**Device markers**

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ECLASS 9.0  | 27-40-06-29 | ECLASS 9.1  | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|

**ESG 10/17 MC SDR**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

