


ET S7-400-TU-A4-3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The ET S7 DIN-A4 non-adhesive labels are used to label the S300, S400 and S7 modules from Siemens. Customised laser printing is possible using Weidmüller's M-Print® Pro software.

- Background colours yellow or turquoise with black printing (boxes)
- Labels can be easily separated (not adhesive)

General ordering data

Version	LaserMark, Device markers, 251 x 13.5 mm, Siemens, Turquoise
Order No.	1865490000
Type	ET S7-400-TU-A4-3
GTIN (EAN)	4032248434169
Qty.	10 pc(s).

ET S7-400-TU-A4-3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.1 mm	Depth (inches)	0.004 inch
Height	251 mm	Height (inches)	9.882 inch
Width	13.5 mm	Width (inches)	0.531 inch
Net weight	31.8 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Application/manufacture	Siemens	
Approval acc. to UL 969	No	
Colour	Turquoise	
Halogen	Yes	
Material	Vinyl film	
Number of markers per combination	1 Label sheet = 14 Device markers	
Number of markers per packaging unit	140	
Number of markers per packaging unit	Number of markers per combination	14
	Number of combinations per packaging unit	10
	Form of supply	Label sheet
Number per sheet	14	
Operating temperature range	-40...80 °C	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Printing method	Laser print	
UL 94 flammability rating	HB	
Width	13.5 mm	

Device markers

Halogen	Yes
---------	-----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

ET S7-400-TU-A4-3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

