

**CC 15/17 MC SDR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

**For custom printing:** Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	ClipCard, Device markers, 15 x 17 mm, Holder CC-H 15/17, To customer specification
Order No.	<a href="#">1876620000</a>
Type	CC 15/17 MC SDR
GTIN (EAN)	4032248467136
Qty.	16 pc(s).
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

**CC 15/17 MC SDR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	1 mm	Depth (inches)	0.039 inch
Height	15 mm	Height (inches)	0.591 inch
Width	17 mm	Width (inches)	0.669 inch
Net weight	2.875 g		

**Temperatures**

Operating temperature range	-40...100 °C
-----------------------------	--------------

**General data**

Application/manufacture	Holder CC-H 15/17	
Colour	To customer specification	
Colour of printing	black	
Halogen	No	
Material	Polyamide 66	
Number of markers per combination	1 MultiCard = Device markers	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40...100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Printed characters	Based on customer requirements (Please send M-Print PRO file)	
Printing method	MC Laser	
UL 94 flammability rating	V-2	
Width	17 mm	

**Device markers**

Halogen	No
---------	----

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

**CC 15/17 MC SDR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**CC 15/17 MC SDR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Accessories****General ordering data**

Type	CC-RAIL 1000	Version
Order No.	<a href="#">1790150000</a>	ClipCard, Accessories, 1000 x 17 mm, Self-adhesive, black
GTIN (EAN)	4032248213610	
Qty.	1 pc(s).	
Type	ETO CC 15/17 TRANSPAR.	Version
Order No.	<a href="#">1880850000</a>	ClipCard, Accessories, 15 x 17 mm, Transparent
GTIN (EAN)	4032248481224	
Qty.	10 pc(s).	
Type	STR CC 15/17 TRANSPARENT	Version
Order No.	<a href="#">1888310000</a>	ClipCard, Accessories, 15 x 17 mm, Transparent
GTIN (EAN)	4032248494187	
Qty.	80 pc(s).	
Type	CC-H 15/17	Version
Order No.	<a href="#">1790430000</a>	ClipCard, Accessories, 15 x 17 mm, black
GTIN (EAN)	4032248215225	
Qty.	75 pc(s).	
Type	CC-RAIL TRANSPARENT1000	Version
Order No.	<a href="#">1790160000</a>	ClipCard, Cover, 1000 x 19 mm, Transparent
GTIN (EAN)	4032248213627	
Qty.	1 pc(s).	