

CC 15/60 MC NE SI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ClipCard, Device markers, 15 x 60 mm, Holder CC-H 15/60, silver
Order No.	1877340000
Type	CC 15/60 MC NE SI
GTIN (EAN)	4032248467976
Qty.	40 pc(s).
Alternative product	1072640000
compatible printer	2715590000 2438520000 2438510000

CC 15/60 MC NE SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.047 inch
Height	15 mm	Height (inches)	0.591 inch
Width	60 mm	Width (inches)	2.362 inch
Net weight	3 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Application/manufacture	Holder CC-H 15/60	
Colour	silver	
Halogen	No	
Material	Polyamide 66	
Number of markers per combination	1 MultiCard = Device markers	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40...100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Printed characters	without	
Recommended industries	Machinery	
UL 94 flammability rating	V-2	
Width	60 mm	

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04
ECLASS 14.0	27-28-11-04		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Product Change Notification	MultiCard Material modification MultiCard Material Modifikation
Catalogues	Catalogues in PDF-format

CC 15/60 MC NE SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



CC 15/60 MC NE SI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories****General ordering data**

Type	CC-RAIL 1000	Version
Order No.	1790150000	ClipCard, Accessories, 1000 x 17 mm, Self-adhesive, black
GTIN (EAN)	4032248213610	
Qty.	1 pc(s).	
Type	STR CC 15/60 TRANSPARENT	Version
Order No.	1888280000	ClipCard, Accessories, 15 x 60 mm, Transparent
GTIN (EAN)	4032248494156	
Qty.	40 pc(s).	
Type	CC-RAIL TRANSPARENT 1000	Version
Order No.	1790160000	ClipCard, Cover, 1000 x 19 mm, Transparent
GTIN (EAN)	4032248213627	
Qty.	1 pc(s).	
Type	ETO CC 15/60 TRANSPAR.	Version
Order No.	1880840000	ClipCard, Accessories, 15 x 60 mm, Transparent
GTIN (EAN)	4032248481217	
Qty.	10 pc(s).	
Type	CC-H 15/60	Version
Order No.	1878910000	ClipCard, Accessories, 15 x 60 mm, black
GTIN (EAN)	4032248473298	
Qty.	25 pc(s).	