

**ETO CC 15/27 TRANSPAR.****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

**General ordering data**

|            |  |
|------------|--|
| Version    | ClipCard, Accessories, 15 x 27 mm, Transparent |
| Order No.  | <a href="#">1880810000</a>                     |
| Type       | ETO CC 15/27 TRANSPAR.                         |
| GTIN (EAN) | 4032248480890                                  |
| Qty.       | 10 pc(s).                                      |

**ETO CC 15/27 TRANSPAR.****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 1 mm   | Depth (inches)  | 0.039 inch |
| Height     | 15 mm  | Height (inches) | 0.591 inch |
| Width      | 27 mm  | Width (inches)  | 1.063 inch |
| Net weight | 11.9 g |                 |            |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

**General data**

|                                      |                             |           |
|--------------------------------------|-----------------------------|-----------|
| Adhesive                             | Permanent acrylic copolymer |           |
| Colour                               | Transparent                 |           |
| Halogen                              | No                          |           |
| Material                             | Polyester film              |           |
| Number of markers per combination    | 1 MultiCard = Accessories   |           |
| Number of markers per packaging unit | Form of supply              | MultiCard |
| Number per sheet                     | 133                         |           |
| Operating temperature range          | -40... 100 °C               |           |
| Operating temperature range, max.    | 100 °C                      |           |
| Operating temperature range, min.    | -40 °C                      |           |
| Recommended industries               | Machinery                   |           |
| UL 94 flammability rating            | V-2                         |           |
| Width                                | 27 mm                       |           |

**Device markers**

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ECLASS 9.0  | 27-40-06-29 | ECLASS 9.1  | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|

**ETO CC 15/27 TRANSPAR.**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

